# **BELCO Medical Tray Sealers**



Packaging Systems, Inc.

800-833-1833

## **BELCO Medical Tray Sealers**

## Total Efficiency... No Ifs, Ands or Bolts

### Standard On All Machines

- Class 10,000 Cleanroom Compatible
- Welded and Powder Coated Tubular **Steel Frame**
- Fully Enclosed Stainless Steel **Seal Chamber**
- Stationary Aluminum Heat Seal Platen
- Platen Heat Shroud
- Temperature Overlimit Safety Circuit
- Teflon Coated Top Tool
- Oiless Air System
- Coalescing Exhaust Filter
- Out of Temperature Alarm
- Validation Ports for Time, Temperature and Pressure (optional item on BM Standard machine models)
- Locking/Non-marring Casters and Leveling Screws (on all floor models)
- Comprehensive Documentation/ **Owner's Manual**

You'll profit from the solid advantages of Belco Medical Tray Sealers. These ruggedly-built machines provide the framework for greater productivity and less maintenance, which means higher profitability for you. Year after year, Belco's durable, heavy-duty, fully-welded tubular steel frames give you dependable performance and consistent results... and that's crucial in the medical packaging industry.

Belco Medical Tray Sealers, reinforced at all pressure points, are built to last. No bolts to loosen and weaken the machine. No shaking and rattling to affect production performance or accuracy. No machine components failing or jamming in critical situations. What you get are total performance medical tray sealers that are simple to operate and easy to maintain.

## **Performance Packaging**

Increased production rates only mean greater productivity if superior quality control is achieved. Belco Medical Tray Sealers utilize proven components that assure you of the highest levels of process control at even the closest tolerances. Cleanroom production environments as well as prototype work benefit from the minimal maintenance, fast tooling setup and repeatability provided by Belco Medical Tray Sealers.

Take a closer look... you'll see how our precision controls and built-in safety features prevent bad seals and compromised

are essential. Belco's one piece top tooling design makes rapid tooling changeovers a reality." *Iim Reimers,* 

"As a contract medical device

manufacturer, the equipment we

use must be versatile and

productive. To optimize produc-

tivity, quick tooling changeovers

Medical Device Manufacturing & Ventures, Inc.

production. For example, the temperature alarm circuit assures that sealing only occurs at the proper temperature. It warns the operator of any temperature differential by not allowing the machine to be cycled. Poor seals can't happen inadvertently. Quite simply, process control is the hallmark of our design philosophy. Our medical tray sealers offer you four levels of sophistication with one unwavering commitment to excellence.

## **Machine Options**

- Extended Seal Chamber Pass **Through Clearances**
- All Stainless Steel Construction
- High Temperature Sealing Package
- High Pressure Sealing Package
- Different Voltages
- Spare Parts Kits
- Custom Platen Sizes
- Custom Engineering
- Custom Manufactured Seal Fixtures
- Start-up Supervision and Training
- CE Certification

## Strength of Product, Strength of Company

It's not surprising that the most accurate... and consequently, most dependable... medical tray sealers on the market are made by Belco Packaging Systems, Inc. The largest manufacturer of medical tray sealing

systems on the West Coast, Belco engineers every product for long life, maximum productivity and adherence to your strictest requirements. Inside and out, from

top to bottom, Belco creates a framework for efficiency... a machine that pays for itself. All Belco machines are backed by our factory service and repair, a friendly, knowledgeable staff and one of the most comprehensive warranties

Welded tubular steel frame



in the industry. We're committed to your total satisfaction. No ifs, ands or bolts.



## **BM Standard - The Solid Framework for Dependability**

### Models BM Standard 2020, BM Standard 3025

When you need productivity, reliability and accuracy, you can count on Belco's BM Standard models. You get consistent quality seals with built-in safety and performance features. Designed to provide operator confidence and process control, these capable units are affordably priced for situations where your primary concerns include both quality and budget.



- Low Air Pressure Safety Switch
- Two Gallon Air Reservoir
- Validation Ports

"We built our new plant from the ground up. We could have chosen any other manufacturers' tray sealers... but we chose Belco. Their frames are built stronger. We have found that they are more dependable and more consistent than any other machine we have ever used."

Don Preecs, Bard Access Systems

TEL: 626-357-9566 ◆ FAX: 626-359-3440

Internet: www.belcopackaging.com ◆ Email: info@belcopackaging.com

800-833-1833

3

Adjustable Leveling Screws prevent

Standard on all floor models.

machine movement during operation.

## andards of Dependability ving on Excellence

## **Typical Information Screens**

### **Start Up and Operational Screens**


- ◆ Keyboard Access
- ◆ Setup Parameter Screen
- ♦ Event Log
- ◆ History Log
- ◆ Cycle Counter
- ◆ Cycle Start
- ◆ Temperature Adjustment
- ◆ Platen 12 point Temperature Monitor
- ◆ Actual Temperature Graph
- ◆ Last Cycle Pressure Graph
- ◆ Temperature Adjustment in Process
- ◆ Open Thermocouple Alarm
- ◆ Pressure Alarm Message
- ♦ Shut Down/Restart

### **Database Setup Screens**

- ◆ Password Database
- ◆ Tool Database Setup
- ◆ Tool Database Editor
- ◆ Product ID Database Editor
- ◆ Seal Fixture Database Editor
- ◆ Matching/Cross Reference to Product ID
- Custom Display Screens

"Belco's Medical Tray Sealers provide an accuracy level we could not get from anyone else's machines. They are simple to calibrate and easy to validate. As such, they are up and running much faster. Belco's philosophy of 'one on one' technical support is excellent."


Larry Brown, Lab Manager Precision Measurement Equipment Services



## **Customized Seal Fixtures**



Belco provides customized seal fixtures for all machine models and sizes. Our staff works closely with you during the design phase and documents the process to assure complete satisfaction. You'll find that our experience in manufacturing, utilizing state of the art equipment and technology, results in seal fixtures of the highest caliber. Our seal fixtures are guaranteed to provide the finest seal quality, consistency and productivity.



TEL: 626-357-9566 ◆ FAX: 626-359-3440

Internet: www.belcopackaging.com ◆ Email: info@belcopackaging.com

## How to choose which Belco Medical Tray Sealer is right for you?

When considering which model Belco Medical Tray Sealer to choose, there are two issues of primary consideration; Sealing Size and Required Levels of Process Control.

**Sealing Size** – The first consideration is the size range of your package components. Do your trays and lids fit within the maximum sealing area for each respective model size?

Other factors may affect and influence your desired results, such as total seal surface area, sealing flange width, thermoform material thickness and consistency. For more specific information, please consult with Belco's experienced and knowledgeable medical sales group.

## **Required Levels of Process Control**

As you step up in performance with each model, you gain an increased level of control and flexibility. The BM PC models add sophisticated levels of data acquisition. No matter which series you choose, all Belco models are capable of delivering the same high quality sealed package.

WARRANTY – The Belco medical tray sealers are built to exacting standards with the finest materials and the most skilled craftsmen. Rugged and durable, the frame is guaranteed for five years. The electrical components have passed precise measurement tests and are guaranteed for one year. The overall performance of your machine is guaranteed for one year on all parts. Extended warranty, preventative maintenance and spare parts kits are available. Belco inventories components and parts for all machines sold.

### Belco Medical Tray Sealer models are available in four levels of process control.

Belco Me	All digital controls All controls conveniently located at operator eye level Independent shuttle(s) time control Validation Ports for time, temperature and pressure System Alarms for temperature and  • Increased PLC control accuracy • Air system pressure validation program • Independent shuttle pressure control for front and rear • Enhanced System Alarms for multiple functions • Internal PC Workstation with Windows NT® operating system • Fully validatable DAQ capabilities • Increased PC control accuracy • Air system pressure validation program • Fully validatable DAQ capabilities • Increased PC control accuracy • Set up and operation security features				
BM STANDARD	BM EL	BM PLC	BM PC		
Cost effective Easy Set up Simple operation Oiless air pressure system Analog and Digital Controls System Alarm for temperature	<ul><li>Independent shuttle(s) time control</li><li>Validation Ports for time, temperature</li></ul>	<ul> <li>Increased PLC control accuracy</li> <li>Air system pressure validation program</li> <li>Independent shuttle pressure control for front and rear</li> <li>Enhanced System Alarms for multiple functions</li> </ul>	Internal PC Workstation with Windows NT® operating system     Fully validatable DAQ capabilities     Increased PC control accuracy for all machine and package parameters     Easy to read/use operator interface		

	BM 2020	BM 3025	BM EL 1010	BM EL 2020	BM El 3025	BM PLC 1010	BM PLC 2020	BM PLC 3025	BM PLC 3830	BM PC 2020	BM PC 3025	BM PC 3830
Maximum Seal Size Fixture	20 x 20"	30 x 25"	10 x 10"	20 x 20"	30 x 25"	10 x 10"	20 x 20"	30 x 25"	38 x 30"	20 x 20"	30 x 25"	38 x 30"
Maximum Tray Depth	3 1/2"	3 1/2"	3 1/2"	3 1/2"	3 1/2"	3 1/2"	3 1/2"	3 1/2"	8"	3 1/2"	3 1/2"	8"
Temperature Control °F	50-300° F	50-300° F	50-300°F	50-300° F	50-300° F	50-300° F	50-300° F	50-300° F	50-300° F	50-300° F	50-300° F	50-300° F
Electrical Requirements												
Voltage	208-240	208-240	120	208-240	208-240	120	208-240	208-240	208-240	208-240	208-240	208-240
Phase	1PH	1PH	1 PH	1PH	1PH	1 PH	1PH	1PH	3PH	1PH	1PH	3PH
Amperage	25	40	15	25	40	15	25	40	45	25	40	45
Hz	50/60	50/60	50/60	50/60	50/60	50/60	50/60	50/60	50/60	50/60	50/60	50/60
Air Requirements												
Maximum Input/PSI	125	125	125	125	125	125	125	125	125	125	125	125
Cubic feet/cycle	0.12	0.24	0.06	0.12	0.24	0.06	0.12	0.24	0.36	0.12	0.24	0.36
Cylinder Bore Size	8"	Dual 8"	4" Double	8"	Dual 8"	4" Double	8"	Dual 8"	Triple 8"	8″	Dual 8"	Triple 8"
Space Requirement												
Height	48	48	34	56	56	34	56	56	66	48	48	56
Width	26	36	18 1/2	26	36	18 1/2	26	36	48	26	36	48
Length	82	97	35	82	97	35	82	97	108	82	97	108
Shipping Weight	625	975	215	625	975	215	625	975	1800	625	975	1800

At Belco we are sensitive to the wants and needs of our customers. Therefore, we reserve the right to make improvements and make changes to specifications without notice.







Belco Packaging Systems, Inc.

910 South Mountain Avenue • Monrovia, California 91016 TEL: 626-357-9566 • FAX: 626-359-3440

> Internet: www.belcopackaging.com Email: info@belcopackaging.com

800-833-1833

Designed and Produced by LTG&A • www.ltga.com • 818-842-027(

© Copyright 2000 — Belco Packaging Systems, Inc. • All Rights Reserved